PHILIPS

Lighting

Essential SmartBright Solar Post Top

BPC010 LED40/MCT Solar post top

A range of solar all in one post top with unique feature of selectable color temperature

Warnings and Safety

• Install the product in a place with adequate sunlight without shades of trees, building, walls etc. for faster charging of battery

Product data

General Information	
Driver included	Yes
Value ladder	Value
Warranty period	1 years

Light Technical	
Luminous Flux	4,000 lm
Correlated Color Temperature (Nom)	3000 4000 6500 K
Luminous Efficacy (rated) (Nom)	165 lm/W
Color rendering index (CRI)	70

Operating and Electrical	
Battery type	Lithium Ferro Phosphate
Battery ampere hour	14.4 Ah
Battery voltage	3.2 V
Panel type	Poly crystalline
Panel voltage	4.5 V
Panel peak wattage	15 W
Grid connection type	Off grid

Controls and Dimming	
Dimmable	Yes
Configurability	Not configurable
Solar dimming profile	Pre-configured

Mechanical and Housing	
Housing Color	Grey
Overall length	420 mm
Overall width	420 mm
Overall height	123 mm
Overall diameter	420 mm
Dimensions (Height x Width x Depth)	123 x 420 x 420 mm
Material	Polycarbonate
Battery location	In built
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Optical cover type	Polycarbonate
Net Weight (Piece)	3.000 kg

Essential SmartBright Solar Post Top

Approval and Application	
Ambient temperature range	0 °C to 55 °C

Over Time Performance (IEC Compliant)	
Median useful life L70B50	25,000 hour(s)

Product Data	
Order product name	BPC010 LED40/MCT Solar post top
Full product name	BPC010 LED40/MCT Solar post top

Full product code	692382866938699
Order code	911401863302
Material Nr. (12NC)	911401863302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828669386
Numerator - Packs per outer box	2
EAN/UPC - Case	6923828669423

Dimensional drawing



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.