PHILIPS

Lighting

StreetStar Gen2

BRP245 LED202/WW 150W DM0 PSU

StreetStar Gen2, 20200 lm, 150 W, 730 warm white, Safety class I, Side-entry for diameter 48 to 60 mm

StreetStar Gen2 brings great value for street lighting with its energy-efficient, cost-effective, slim but robust design. It's the perfect option for municipalities and businesses seeking a reliable and sustainable lighting solution. StreetStar Gen2 offers unparalleled value and performance.

Product data

General Information	
Gear	EB [Electronic]
Driver included	Yes
Light source engine type	LED
Value ladder	Value

Light Technical	
Luminous Flux	20,200 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	135 lm/W
Color rendering index (CRI)	≥70
Light source color	730 warm white
Effective projected area	0.104 m²

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	54 A
Power Consumption	150 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	Cable without plug 3-pole
Number of products on MCB of 16 A type B	7
Protection class IEC	Safety class I

Controls and Dimming	
Dimmable	Fixed
Control interface	-
Maximum dim level	Not applicable

Mechanical and Housing	
Housing Material	Aluminum die-cast
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Glass
Housing Color	RAL7040
Mounting device	Side-entry for diameter 48 to 60 mm
Optical cover finish	Clear

StreetStar Gen2

Overall length	655 mm
Overall width	210 mm
Overall height	81 mm
Dimensions (Height x Width x Depth)	81 x 210 x 655 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [6 J]
Optical cover type	Tempered glass
Net Weight (Piece)	2.250 kg

Approval and Application

Flammability mark	-
CE mark	Yes
ENEC mark	-
EU RoHS compliant	Yes
Performance ambient temperature Tq	35 °C
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.33,0.40) SDCM<5
Power consumption tolerance	+/-10%

Application Conditions

Lumen Maintenance	50000hrs

Product Data

Order product name	BRP245 LED202/WW 150W DM0 PSU
Full product name	BRP245 LED202/WW 150W DM0 PSU
Full product code	872110330417900
Order code	911401868487
Material Nr. (12NC)	911401868487
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103304179
Numerator - Packs per outer box	1
EAN/UPC - Case	8721103304179

Dimensional drawing



© 2025 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.