



Trunklinea Plus

31600 Trunklinea Plus LED12/WW L1200 GM

Trunklinea Plus, 13 W, 1100 lm, 6500 K

The new Philips Trunklinea Plus offers exceptional value. It is Perfect for your everyday lighting installations. Available in 4 standard sizes and 3 CCTs to provide flexibility to customer. It provide quality light and substantial energy and maintenance savings. This new batten range can be used to replace traditional battens with T5 fluorescent lamps.

Product data

General Information		Control interface	
Light source engine type	LED		-
Light Technical		Mechanical and Housing	
Luminous Flux	1,100 lm	Housing Material	Polycarbonate
Correlated Color Temperature (Nom)	6500 K	Optical cover material	Polycarbonate
Luminous Efficacy (rated) (Nom)	80 lm/W	Housing Color	White
Color rendering index (CRI)	>70	Optical cover finish	Opal
Light source color	730 warm white	Overall length	1,185 mm
Operating and Electrical		Overall width	21 mm
Input Voltage	220 to 240 V	Overall height	32.3 mm
Line Frequency	50 or 60 Hz	Dimensions (Height x Width x Depth)	32 x 21 x 1185 mm
Power Consumption	13 W	Ingress protection code	IP20 [Finger-protected]
Power Factor (Fraction)	0.5	Mech. impact protection code	IK02 [0.2 J standard]
Number of products on MCB of 16 A type B 8		Optical cover type	Opal diffuser in polycarbonate cover
Protection class IEC	Safety class II	Net Weight (Piece)	0.140 kg
Controls and Dimming		Approval and Application	
Dimmable	No	CE mark	No
		Ambient temperature range	-20 to +40 °C

Trunklinea Plus

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	31600 Trunklinea Plus LED12/WW L1200 GM
Full product name	31600 Trunklinea Plus LED12/WW L1200 GM

Full product code	871016335547499
Order code	911401868980
Material Nr. (12NC)	911401868980
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163355474
Numerator - Packs per outer box	40
EAN/UPC - Case	8710163355719

Dimensional drawing

