



# CoreLine Wall-mounted

## WL140Z Half-moon Ring BK

- V, Black

CoreLine wall-mounted solutions deliver on the CoreLine promise of innovative, easy-to-install and high-quality luminaires. These circular-shaped, surface-mounted luminaires are suitable for both ceiling and wall installations and are easy to apply in circulation areas such as corridors, hallways and staircases. The modern, unobtrusive design, combined with a homogeneous light distribution, ensures this luminaire will blend into the architecture of most buildings. All-in features provide up to three lumen packages and three colour temperature options in one luminaire. Installers can easily fit the luminaire according to the application need on site. And thanks to the push-in connectors, installation of the CoreLine WL140V is fast and straightforward. This family includes Interact ready luminaires with integrated wireless communications, ready for use with Interact gateways, sensors and software.

### Warnings and Safety

- For outdoor operations; wall-mounted applications only and all cables should run indoors with a maximum distance of 10 metres

### Product data

General Information		Protection class IEC	
Value ladder	Performance		-
Operating and Electrical		Mechanical and Housing	
Input Voltage	- V	Overall length	390 mm
Line Frequency	- Hz	Overall width	390 mm
		Overall height	88 mm
		Overall diameter	390 mm

## CoreLine Wall-mounted

Dimensions (height x width x depth)	88 x 390 x 390 mm
Material	Polycarbonate
Ingress protection code	-
Mech. impact protection code	-
Accessory colour	Black
Angle	-
Net Weight (Piece)	0.740 kg

### Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

### Product Data

Order product name	WL140Z Half-moon Ring BK
Full product name	WL140Z Half-moon Ring BK
Full EOC	871951453565799
Order code	911401873082
Material no. (12 NC)	911401873082
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514535657
Numerator – packs per outer box	6
EAN/UPC – Case	8719514535701

