

WL140Z Half-moon Ring BK

911401873082



Install smarter, finish sooner Choose long-lasting reliability and performance

CoreLine wall-mounted solutions deliver on the CoreLine promise of innovative, easy-to install and high-quality luminaires. These circular-shaped, surface-mounted luminaires are suitable for both ceiling and wall installations and are easy to apply in circulation areas such as corridors, hallways and staircases. The modern, unobtrusive design, combined with a homogeneous light distribution, ensures this luminaire will blend into the architecture of most buildings. All-in features provide up to three lumen packages and three color temperature options in one luminaire. Installers can easily fit the luminaire according to the application need on site. And thanks to the push-in connectors, installation of the CoreLine WL140V is fast and straightforward. This family includes Interact ready luminaires with integrated wireless communications, ready for use with Interact gateways, sensors and software.

Warnings and Safety

- For outdoor operations; wall-mounted applications only and all cables should run indoors with a maximum distance of 10 meters

General Information

Value ladder	Performance
--------------	-------------

Operating and Electrical

Input Voltage	- V
Line Frequency	- Hz
Protection class IEC	-

Mechanical and Housing

Overall length	390 mm
Overall width	390 mm
Overall height	88 mm
Overall diameter	390 mm
Dimensions (Height x Width x Depth)	88 x 390 x 390 mm
Material	Polycarbonate
Ingress protection code	-
Mech. impact protection code	-
Accessory color	Black
Angle	-
Net Weight (Piece)	0.740 kg

Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

Sustainability Data

Non-virgin material ratio of the packaging	Cardboard > 80% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80%
Packaging Material	Cardboard

Product Data

Order product name	WL140Z Half-moon Ring BK
Full product name	WL140Z Half-moon Ring BK
Full product code	871951453565799
Order code	911401873082
Material Nr. (12NC)	911401873082
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514535657
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514535701