



CoreLine Wall-mounted

WL140Z Half-moon Ring GR

- V, Gray

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Wall-mounted range of LED products can be used to replace traditional wall-mounted luminaires incorporating compact fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Warnings and Safety

- For outdoor operations; wall-mounted applications only and all cables should run indoors with a maximum distance of 10 meters

Product data

General Information		Dimensions (Height x Width x Depth)	
Value ladder	Performance	88 x 390 x 390 mm	
Operating and Electrical		Material	Polycarbonate
Input Voltage	- V	Ingress protection code	-
Line Frequency	- Hz	Mech. impact protection code	-
Protection class IEC	-	Accessory color	Gray
Mechanical and Housing		Angle	-
Overall length	390 mm	Net Weight (Piece)	0.740 kg
Overall width	390 mm	Approval and Application	
Overall height	88 mm	CE mark	Yes
Overall diameter	390 mm	EU RoHS compliant	Yes

CoreLine Wall-mounted

Sustainability Data

Non-virgin material ratio of the packaging Cardboard > 80% recycled Plastic >35% recycled

Packaging Recyclable content ratio Cardboard recycling rate > 80% Plastic recycling rate > 40%

Packaging Material Cardboard Plastic

Product Data

Order product name WL14OZ Half-moon Ring GR

Full product name WL14OZ Half-moon Ring GR

Full product code 871951453566499

Order code 911401873182

Material Nr. (12NC) 911401873182

Numerator - Quantity Per Pack 1

EAN/UPC - Product/Case 8719514535664

Numerator - Packs per outer box 6

EAN/UPC - Case 8719514535718

