



Essential SmartBright Solar Flood

BVC080 LED30/730 Solar

Solar flood light with lithium ferro phosphate battery built in the luminaire, Remote controller and installation accessories included. IP65, plastic housing. Available in 600, 900, 1500, 2500, 3000 and 4000 Lumens

Warnings and Safety

- Install the luminaire in a sunny place that is not shaded by trees, buildings and walls, then the solar panel can receive the maximum sunlight for charging the battery.
- Charge the product under sunlight for at least 8 hours before first time using.
- This luminaire does not need any external electrical connection. It works 100% on solar energy.

Product data

General Information	
Driver included	Yes
Value ladder	Value

Light Technical	
Luminous Flux	3,000 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	140 lm/W
Color rendering index (CRI)	70

Operating and Electrical	
Battery type	LiFePO4
Battery ampere hour	19 Ah
Battery voltage	3.2 V
Battery charging & discharging cycles	500
Panel type	Mono crystalline

Panel voltage	5 V
Panel peak wattage	20 W
Grid connection type	Off grid

Controls and Dimming	
Dimmable	No
Configurability	Not configurable
Solar dimming profile	Pre-configured

Mechanical and Housing	
Housing Color	Grey
Overall length	290 mm
Overall width	249 mm
Overall height	49 mm
Dimensions (Height x Width x Depth)	49 x 249 x 290 mm
Material	Acrylonitrile-butadiene-styrene

Essential SmartBright Solar Flood

Battery location	In built
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Optical cover type	Glass
Net Weight (Piece)	3.700 kg
Approval and Application	
Ambient temperature range	0 °C to 50 °C
Product Data	
Order product name	BVC080 LED30/730 Solar

Full product name	BVC080 LED30/730 Solar
Full product code	692382867166299
Order code	911401875302
Material Nr. (12NC)	911401875302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828671662
Numerator - Packs per outer box	5
EAN/UPC - Case	6923828671723

Dimensional drawing

