



SmartBright Solar All-in-one Pathway

BRC010 M LED10/765 solar

Integrated solar street light with Lithium Ferro Phosphate battery, solar panel and charger built into the luminaire. Metal housing, Wall mounting kit option. Microwave based motion sensor

Warnings and Safety

- Not recommended to install this luminaire higher than 4 meters height.
- Factory set dimming profile along with microwave sensor for run time maximization.

Product data

General Information	
Driver included	Yes
Value ladder	Value
Light Technical	
Luminous Flux	1,000 lm
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	150 lm/W
Color rendering index (CRI)	70
Operating and Electrical	
Battery type	LiFePO4
Battery ampere hour	5 Ah
Battery voltage	3.2 V
Battery charging & discharging cycles	500
Panel type	Poly crystalline
Panel voltage	4.5 V
Panel peak wattage	6 W


Grid connection type	Off grid
Controls and Dimming	
Dimmable	No
Configurability	Not configurable
Solar dimming profile	Pre-configured
Mechanical and Housing	
Housing Color	Silver Grey
Overall length	273 mm
Overall width	183 mm
Overall height	60 mm
Dimensions (Height x Width x Depth)	60 x 183 x 273 mm
Material	Metal
Battery location	In built
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Optical cover type	PS

SmartBright Solar All-in-one Pathway

Net Weight (Piece)	1.100 kg
Approval and Application	
Ambient temperature range	0 °C to 45 °C
Product Data	
Order product name	BRC010 M LED10/765 solar
Full product name	BRC010 M LED10/765 solar
Full product code	692382867174799

Order code	911401875502
Material Nr. (12NC)	911401875502
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828671747
Numerator - Packs per outer box	16
EAN/UPC - Case	6923828671808

Dimensional drawing



TYPE	W(mm)	L(mm)	H(mm)	D(mm)
1000lm	187	281	64	38
2000lm	187	397	64	48
4000lm	225	515	64	48

