



# Essential SmartBright Solar Wall Light

## BWS010 LED05/765 G2

Outdoor solar wall light with inbuilt lithium ferro phosphate battery, solar panel, inbuilt motion sensor, switch to change modes and LED lights integrated in ABS plastic housing.

### Warnings and Safety

- This product includes rechargeable batteries which must be adequately charged under sunlight before use.

### Product data

General Information		Charge controller type	
Driver included	Yes	Charge controller wattage	PWM
Value ladder	Value	Connection	-
Warranty period	1 years	Cable	-
Light Technical		Grid connection type	Off grid
Luminous Flux	50 lm	Controls and Dimming	
Correlated Color Temperature (Nom)	6500 K	Dimmable	Yes
Luminous Efficacy (rated) (Nom)	100 lm/W	Configurability	Not configurable
Color rendering index (CRI)	>70	Control interface	-
Operating and Electrical		Solar dimming profile	As per mode switch
Battery type	Lithiumion - NMC	Mechanical and Housing	
Battery ampere hour	1.2 Ah	Housing Color	Gray
Battery voltage	3.7 V	Overall length	125 mm
Battery charging & discharging cycles	500	Overall width	50 mm
Panel type	Poly crystalline	Overall height	105 mm
Panel voltage	5.5 V	Dimensions (Height x Width x Depth)	105 x 50 x 125 mm
Panel peak wattage	0.5 W	Material	Acrylonitrile-butadiene-styrene

# Essential SmartBright Solar Wall Light

Battery location	Inbuilt
Ingress protection code	IP54 [Dust accumulation-protected, splash-proof]

Optical cover type	Without lens
Net Weight (Piece)	0.170 kg

## Approval and Application

CE mark	Yes
Ambient temperature range	0 °C to 45 °C

## Over Time Performance (IEC Compliant)

Median useful life L70B50	25,000 hour(s)
---------------------------	----------------

## Application Conditions

Ambient temperature range for charging	0 °C to 45 °C
--	---------------

Ambient temperature range for discharging (when light is on)	0 °C to 45 °C
--	---------------

## Product Data

Order product name	BWS010 LED05/765 G2
Full product name	BWS010 LED05/765 G2
Full product code	692382861075399
Order code	911401877202
Material Nr. (12NC)	911401877202
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828610753
Numerator - Packs per outer box	50
EAN/UPC - Case	6923828610784

## Dimensional drawing

