



SmartBright Plus Panel

RC048B+ LED35S/840 PSU W60L60 G2

SmartBright Plus Panel, 130 lm/W, 840 neutral white

The Philips SmartBright Plus panel (RC048B+) range features a selection of popular off-the-shelf LED luminaires that come with Philips high quality levels at a competitive price. Reliable, high energy efficient and affordable, this latest generation of SmartBright Plus LED panel lights are designed for diffuse, comfortable lighting in a wide range of general lighting applications. Our range of SmartBright Plus panel lighting is also available with accessories for easy installation on different types of ceilings – just what you need.

Product data

General Information	
Light source engine type	LED
Value ladder	Value

Light Technical	
Luminous Flux	3,500 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	130 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white
Unified glare rating CEN	23

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz

Power Consumption	26.5 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	35
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	No
Control interface	-

Mechanical and Housing	
Housing Material	Steel
Optical cover material	Polystyrene
Housing Color	White RAL 9003
Optical cover finish	Frosted
Ingress protection code	IP20/40 [Finger-protected, Emitting surface]

SmartBright Plus Panel

Mech. impact protection code	IK02 [0.2 J standard]
Optical cover type	PS
Net Weight (Piece)	1.300 kg
Approval and Application	
CE mark	Yes
Ambient temperature range	-10 to +40 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	-10% / +10%
Power consumption tolerance	+/-10%

Product Data	
Order product name	RC048B+ LED35S/840 PSU W60L60 G2
Full product name	RC048B+ LED35S/840 PSU W60L60 G2
Full product code	872110330987799
Order code	911401880387
Material Nr. (12NC)	911401880387
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103309877
Numerator - Packs per outer box	6
EAN/UPC - Case	8721103309877

Dimensional drawing

