



Essential Smartbright Projector (Wide Voltage) Gen 2

ST033T LED9/840 10W 110-240V I MB BK TW

Essential Smartbright Projector (Wide Voltage) Gen 2, 10 W, 900 lm, 4000 K

Essential SmartBright Projector ST033T is a value for money product designed for Mass market trade. It is designed to replace halogen and CDM-standard-based projectors for retail and hospitality applications. This track based luminaire supports retailers to let their products stand out, or highlight certain objects. The clean and contemporary design with integrated driver makes the Essential SmartBright Projector relevant to many applications. The choice of 2 colors in White and Black helps the Retailer to choose products best suited to blend into the Store Environment. Compared to it's predecessor, it is not only cost effective, but also a more sleek and lighter product design.

Product data

| General Information | | Light source color | |
|------------------------------------|---------|--|--------------|
| Light source engine type | LED | 840 neutral white | |
| Value ladder | Value | | |
| Light Technical | | Operating and Electrical | |
| Luminous Flux | 900 lm | Input Voltage | 110 to 240 V |
| Correlated Color Temperature (Nom) | 4000 K | Line Frequency | 50 or 60 Hz |
| Luminous Efficacy (rated) (Nom) | 90 lm/W | Inrush current | 6 A |
| Color rendering index (CRI) | >80 | Power Consumption | 10 W |
| | | Power Factor (Fraction) | 0.9 |
| | | Number of products on MCB of 16 A type B | 115 |

Essential Smartbright Projector (Wide Voltage) Gen 2

| | |
|-------------------------------------|---|
| Protection class IEC | Safety class II |
| Controls and Dimming | |
| Dimmable | No |
| Control interface | - |
| Mechanical and Housing | |
| Housing Material | Aluminum |
| Optical cover material | Polycarbonate |
| Housing Color | Black |
| Optical cover finish | Textured |
| Overall length | 192 mm |
| Overall width | 129 mm |
| Overall height | 49 mm |
| Overall diameter | 49 mm |
| Dimensions (Height x Width x Depth) | 49 x 129 x 192 mm |
| Ingress protection code | IP20 [Finger-protected] |
| Mech. impact protection code | IK03 [0.3 J] |
| Optical cover type | Collimator with focus angle 24° |
| Net Weight (Piece) | 0.197 kg |
| Approval and Application | |
| Flammability mark | For mounting on normally flammable surfaces |

| | |
|--|---|
| CE mark | No |
| Ambient temperature range | -20 to +45 °C |
| Initial Performance (IEC Compliant) | |
| Luminous flux tolerance | +/-10% |
| Initial chromaticity | (0.3818, 0.3797) SDCM <5 |
| Power consumption tolerance | +/-10% |
| Product Data | |
| Order product name | ST033T LED9/840 10W 110-240V I MB BK TW |
| Full product name | ST033T LED9/840 10W 110-240V I MB BK TW |
| Full product code | 871951454612799 |
| Order code | 911401892982 |
| Material Nr. (12NC) | 911401892982 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8719514546127 |
| Numerator - Packs per outer box | 48 |
| EAN/UPC - Case | 8719514546288 |

Dimensional drawing

