



# CoreLine Fastset, surface-mounted

## SM155Z Besa Bracket

CoreLine Fastset, surface-mounted, Accessory

Philips CoreLine FastSet is a 1:1 energy-efficient LED replacement for conventional indoor surface-mounted lights. With identical lumen packages to fluorescent lighting, there's no need to make new lighting calculations for retrofit projects – thanks to the all-in-one design, you can switch between correlated color temperatures (CCT) and lumen package in the same luminaire to suit your exact needs. Installation of these surface-mounted LED lights is fast and flexible too with a choice of simple through-wiring, or cable entry from the side or back of the luminaire. That means CoreLine FastSet indoor surface-mounted lights are easy to mount as a standalone fixture, directly to the surface-mounted or using brackets. You can also create a line of light due to straight end-caps with head to head mounting. It is also easy to connect them to other CoreLine Fastset luminaires to create harmonious lines of light. Should you require it, accessories are also available to adapt the CoreLine fixtures for suspended mounting. As you'd expect from Philips, safety is designed into every CoreLine FastSet luminaire. Not only are the IP44 and IK06 rated to protect against accidental impact, the captive safety pins on the luminaire cover also prevents it from falling. Interact Ready options are available for smart lighting applications. So with CoreLine FastSet surface-mounted LED lights, you have the perfect solution for high circulation areas such as hallways and staircase lighting.

### Product data

General Information	
Value ladder	Performance

Mechanical and Housing	
Overall length	62 mm
Overall width	48 mm

## CoreLine Fastset, surface-mounted

Overall height	16.8 mm
Dimensions (Height x Width x Depth)	17 x 48 x 62 mm
Material	Stainless steel
Ingress protection code	-
Mech. impact protection code	-
Accessory color	Steel
Net Weight (Piece)	0.010 kg

### Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

### Sustainability Data

Non-virgin material ratio of the packaging	Cardboard > 80% recycled Plastic >35% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80% Plastic recycling rate > 40%

Packaging Material	Cardboard Plastic
--------------------	-------------------

### Product Data

Order product name	SM155Z Besa Bracket
Full product name	SM155Z Besa Bracket
Full product code	872016973702099
Order code	911401892985
Material Nr. (12NC)	911401892985
Numerator - Quantity Per Pack	2
EAN/UPC - Product/Case	8720169737020
Numerator - Packs per outer box	16
EAN/UPC - Case	8720169737037

## Dimensional drawing

