

SM155Z Besa Bracket

911401892985



CoreLine FastSet, surface-mounted, Accessory

Philips CoreLine FastSet is a 1:1 energy-efficient LED replacement for conventional indoor surface-mounted luminaires. With identical lumen packages to fluorescent lighting, there's no need to make new lighting calculations for retrofit projects – thanks to the all-in-one design, you can switch between correlated color temperatures (CCT) and lumen package in the same luminaire to suit your exact needs. Installation of these surface-mounted LED luminaires is fast and flexible too, with a choice of simple through-wiring, or cable entry from the side or rear of the luminaire. That means CoreLine FastSet indoor surface-mounted luminaires are easy to mount as standalone fittings, either directly onto the surface or using brackets. You can also create a line of light thanks to straight end-caps with head to head mounting. It is also easy to connect them to other CoreLine Fastset luminaires to create harmonious lines of light. Should you require it, accessories are also available to adapt the CoreLine fixtures for suspended mounting. As you'd expect from Philips, safety is designed into every CoreLine FastSet luminaire. Not only are the IP44 and IK06 rated to protect against accidental impact, the captive safety pins on the luminaire cover also prevent it from falling. Interact Ready options are available for smart lighting applications. So with CoreLine FastSet surface-mounted LED luminaires, you have the perfect solution for high-traffic areas such as corridors and staircase lighting.

General Information

Value ladder	Performance
--------------	-------------

Mechanical and Housing

Overall length	62 mm
Overall width	48 mm
Overall height	16.8 mm
Dimensions (height x width x depth)	17 x 48 x 62 mm
Material	Stainless steel
Ingress protection code	-
Mech. impact protection code	-
Accessory colour	Steel
Net Weight (Piece)	0.010 kg


Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

Product Data

Order product name	SM155Z Besa Bracket
Full product name	SM155Z Besa Bracket
Full EOC	872016973702099
Order code	911401892985
Material no. (12 NC)	911401892985
Numerator – quantity per pack	2
EAN/UPC — Product/Case	8720169737020
Numerator – packs per outer box	16
EAN/UPC - Case	8720169737037

Dimensional drawing



Related Documents

Documents and certificates	Document Name	Download
Tender text	Tender_Text_911401892985_en_GB.txt	Download 

