

## SM155Z Besa Bracket

911401892985



## CoreLine FastSet, surface-mounted, Accessory

Philips CoreLine FastSet is a 1:1 energy-efficient LED replacement for conventional indoor surface-mounted luminaires. With identical lumen packages to fluorescent lighting, there's no need to make new lighting calculations for retrofit projects – thanks to the all-in-one design, you can switch between correlated color temperatures (CCT) and lumen package in the same luminaire to suit your exact needs. Installation of these surface-mounted LED luminaires is fast and flexible too, with a choice of simple through-wiring, or cable entry from the side or rear of the luminaire. That means CoreLine FastSet indoor surface-mounted luminaires are easy to mount as standalone fittings, either directly onto the surface or using brackets. You can also create a line of light thanks to straight end-caps with head to head mounting. It is also easy to connect them to other CoreLine Fastset luminaires to create harmonious lines of light. Should you require it, accessories are also available to adapt the CoreLine fixtures for suspended mounting. As you'd expect from Philips, safety is designed into every CoreLine FastSet luminaire. Not only are the IP44 and IK06 rated to protect against accidental impact, the captive safety pins on the luminaire cover also prevent it from falling. Interact Ready options are available for smart lighting applications. So with CoreLine FastSet surface-mounted LED luminaires, you have the perfect solution for high-traffic areas such as corridors and staircase lighting.

## General Information

|              |             |
|--------------|-------------|
| Value ladder | Performance |
|--------------|-------------|

## Mechanical and Housing

|                                     |                 |
|-------------------------------------|-----------------|
| Overall length                      | 62 mm           |
| Overall width                       | 48 mm           |
| Overall height                      | 16.8 mm         |
| Dimensions (height x width x depth) | 17 x 48 x 62 mm |
| Material                            | Stainless steel |
| Ingress protection code             | -               |
| Mech. impact protection code        | -               |
| Accessory colour                    | Steel           |
| Net Weight (Piece)                  | 0.010 kg        |


## Approval and Application

|                   |     |
|-------------------|-----|
| CE mark           | Yes |
| EU RoHS compliant | Yes |

## Product Data

|                                 |                     |
|---------------------------------|---------------------|
| Order product name              | SM155Z Besa Bracket |
| Full product name               | SM155Z Besa Bracket |
| Full EOC                        | 872016973702099     |
| Order code                      | 911401892985        |
| Material no. (12 NC)            | 911401892985        |
| Numerator – quantity per pack   | 2                   |
| EAN/UPC — Product/Case          | 8720169737020       |
| Numerator – packs per outer box | 16                  |
| EAN/UPC - Case                  | 8720169737037       |

Dimensional drawing



Related Documents

| Documents and certificates | Document Name                      | Download                                                                                                       |
|----------------------------|------------------------------------|----------------------------------------------------------------------------------------------------------------|
| Tender text                | Tender_Text_911401892985_en_IE.txt | <a href="#">Download</a>  |

