



Essential SmartBright All-in-one Solar Pathway

BRC010 LED20/730 Pro G2

Integrated solar pathway light with Lithium Ferro Phosphate battery, solar panel and charger built into the luminaire. Optional wall mounting arm bracket. Microwave based motion sensor for optimizing battery autonomy.

Warnings and Safety

- Not recommended to install this luminaire higher than 4 meters height.
- Install the luminaire in a sunny place that is not shaded by trees, buildings and walls, then the solar panel can receive the maximum sunlight for charging the battery.
- Charge the product under sunlight for at least 8 hours before first time using.
- It works 100% on solar energy. This luminaire does not need any external electrical connection.

Product data


General Information		Operating and Electrical	
Driver included	Yes	Line Frequency	- Hz
Value ladder	Value	Battery type	LiFePO4
Warranty period	2 years	Battery ampere hour	8 Ah
		Battery voltage	3.2 V
		Battery charging & discharging cycles	1000
		Panel type	Mono crystalline
		Panel voltage	4.5 V
		Panel peak wattage	8 W
		Charge controller type	PWM
		Connection	-
		Cable	-

Essential SmartBright All-in-one Solar Pathway

Grid connection type	Off grid
Controls and Dimming	
Dimmable	Preset Dimming
Configurability	Not configurable
Control interface	-
Solar dimming profile	Preset Dimming
Mechanical and Housing	
Housing Color	Grey
Overall length	412 mm
Overall width	203 mm
Overall height	44.5 mm
Dimensions (Height x Width x Depth)	45 x 203 x 412 mm
Material	Polycarbonate
Battery location	Inbuilt luminaire
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Optical cover type	Polycarbonate
Net Weight (Piece)	1.310 kg

Approval and Application	
CE mark	Yes
EU RoHS compliant	Yes
Ambient temperature range	0 to +45 °C
Product Data	
Order product name	BRC010 LED20/730 Pro G2
Full product name	BRC010 LED20/730 Pro G2
Full product code	872016976559799
Order code	911401898202
Material Nr. (12NC)	911401898202
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169765597
Numerator - Packs per outer box	5
EAN/UPC - Case	8720169766198

Dimensional drawing



	Unit: mm			
TYPE	W	L	H	D
1000lm	171	371	44.5	40
2000lm	203	412	44.5	50
4000lm	228	508	44.5	50

