



Coreline Slim Batten

BN126C LED22S/840 PSU L600

Coreline Slim Batten, 17 W, 2200 lm, 4000 K

The new Philips Coreline slim batten offers exceptional value. It is Perfect for your everyday lighting installations. Available in 3 standard sizes, and 2 CCTs to provide flexibility to customer.

Product data

General Information		Control interface	
Light source engine type	LED		-
Service tag	Yes		
Light Technical		Mechanical and Housing	
Luminous Flux	2,200 lm	Housing Material	Steel
Correlated Color Temperature (Nom)	4000 K	Optical cover material	Polycarbonate
Luminous Efficacy (rated) (Nom)	105 lm/W	Housing Color	White RAL 9003
Color rendering index (CRI)	>80	Optical cover finish	Opal
Light source color	840 neutral white	Overall length	600 mm
		Overall width	65 mm
		Overall height	65 mm
		Dimensions (Height x Width x Depth)	65 x 65 x 600 mm
Operating and Electrical		Ingress protection code	IP20/40 [Finger-protected;Wire-protected]
Input Voltage	220 to 240 V	Mech. impact protection code	IK04 [0.5 J standard plus]
Line Frequency	50 or 60 Hz	Optical cover type	Polycarbonate Diffuser
Power Consumption	17 W	Net Weight (Piece)	0.520 kg
Power Factor (Fraction)	0.9		
Number of products on MCB of 16 A type B	80	Approval and Application	
Protection class IEC	Safety class I	CE mark	Yes
		Ambient temperature range	-20 to +40 °C
Controls and Dimming			
Dimmable	No		

Coreline Slim Batten

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	BN126C LED22S/840 PSU L600
Full product name	BN126C LED22S/840 PSU L600
Full product code	692382863851199

Order code	911401898780
Material Nr. (12NC)	911401898780
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828638511
Numerator - Packs per outer box	8
EAN/UPC - Case	6923828638573

Dimensional drawing

