



Coreline Slim Batten

BN126C LED41S/865 PSU L1200

Coreline Slim Batten, 31 W, 4100 lm, 6500 K

The new Philips Coreline slim batten offers exceptional value. It is Perfect for your everyday lighting installations. Available in 3 standard sizes, and 2 CCTs to provide flexibility to customer.

Product data

General Information	
Light source engine type	LED
Service tag	Yes
Light Technical	
Luminous Flux	4,100 lm
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	105 lm/W
Color rendering index (CRI)	>80
Light source color	865 cool daylight
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	31 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	45
Protection class IEC	Safety class I
Controls and Dimming	
Dimmable	No

Control interface	-
Mechanical and Housing	
Housing Material	Steel
Optical cover material	Polycarbonate
Housing Color	White RAL 9003
Optical cover finish	Opal
Overall length	1,135 mm
Overall width	65 mm
Overall height	65 mm
Dimensions (Height x Width x Depth)	65 x 65 x 1135 mm
Ingress protection code	IP20/40 [Finger-protected;Wire-protected]
Mech. impact protection code	IK04 [0.5 J standard plus]
Optical cover type	Polycarbonate Diffuser
Net Weight (Piece)	0.850 kg
Approval and Application	
CE mark	Yes
Ambient temperature range	-20 to +40 °C

Coreline Slim Batten

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	BN126C LED41S/865 PSU L1200
Full product name	BN126C LED41S/865 PSU L1200
Full product code	692382863854299
Order code	911401899080

Material Nr. (12NC)	911401899080
Local order code	BN12641L8654FT
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828638542
Numerator - Packs per outer box	8
EAN/UPC - Case	6923828638603

Dimensional drawing

