



Coreline Slim Batten

BN126C LED60S/840 PSU L1500

Coreline Slim Batten, 46 W, 6000 lm, 4000 K

The new Philips Coreline slim batten offers exceptional value. It is Perfect for your everyday lighting installations. Available in 3 standard sizes, and 2 CCTs to provide flexibility to customer.

Product data

General Information		Control interface	
Light source engine type	LED		-
Service tag	Yes		
Light Technical		Mechanical and Housing	
Luminous Flux	6,000 lm	Housing Material	Steel
Correlated Color Temperature (Nom)	4000 K	Optical cover material	Polycarbonate
Luminous Efficacy (rated) (Nom)	105 lm/W	Housing Color	White RAL 9003
Color rendering index (CRI)	>80	Optical cover finish	Opal
Light source color	840 neutral white	Overall length	1,450 mm
Operating and Electrical		Overall width	65 mm
Input Voltage	220 to 240 V	Overall height	65 mm
Line Frequency	50 or 60 Hz	Dimensions (Height x Width x Depth)	65 x 65 x 1450 mm
Power Consumption	46 W	Ingress protection code	IP20/40 [Finger-protected;Wire-protected]
Power Factor (Fraction)	0.9	Mech. impact protection code	IK04 [0.5 J standard plus]
Number of products on MCB of 16 A type B	30	Optical cover type	Polycarbonate Diffuser
Protection class IEC	Safety class I	Net Weight (Piece)	1.040 kg
Controls and Dimming		Approval and Application	
Dimmable	No	CE mark	Yes
		Ambient temperature range	-20 to +40 °C

Coreline Slim Batten

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	BN126C LED60S/840 PSU L1500
Full product name	BN126C LED60S/840 PSU L1500
Full product code	692382863855999

Order code	911401899180
Material Nr. (12NC)	911401899180
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828638559
Numerator - Packs per outer box	6
EAN/UPC - Case	6923828638610

Dimensional drawing

