



# Coreline Slim Batten

## BN126C LED60S/840 PSU L1500

Coreline Slim Batten, 46 W, 6000 lm, 4000 K

The new Philips Coreline slim batten offers exceptional value. It is Perfect for your everyday lighting installations. Available in 3 standard sizes, and 2 CCTs to provide flexibility to customer.

### Product data

|                                          |                   |
|------------------------------------------|-------------------|
| General Information                      |                   |
| Light source engine type                 | LED               |
| Service tag                              | Yes               |
| Light Technical                          |                   |
| Luminous Flux                            | 6,000 lm          |
| Correlated Color Temperature (Nom)       | 4000 K            |
| Luminous Efficacy (rated) (Nom)          | 105 lm/W          |
| Color rendering index (CRI)              | >80               |
| Light source color                       | 840 neutral white |
| Operating and Electrical                 |                   |
| Input Voltage                            | 220 to 240 V      |
| Line Frequency                           | 50 or 60 Hz       |
| Power Consumption                        | 46 W              |
| Power Factor (Fraction)                  | 0.9               |
| Number of products on MCB of 16 A type B | 30                |
| Protection class IEC                     | Safety class I    |
| Controls and Dimming                     |                   |
| Dimmable                                 | No                |

|                                     |                                           |
|-------------------------------------|-------------------------------------------|
| Control interface                   | -                                         |
| Mechanical and Housing              |                                           |
| Housing Material                    | Steel                                     |
| Optical cover material              | Polycarbonate                             |
| Housing Color                       | White RAL 9003                            |
| Optical cover finish                | Opal                                      |
| Overall length                      | 1,450 mm                                  |
| Overall width                       | 65 mm                                     |
| Overall height                      | 65 mm                                     |
| Dimensions (Height x Width x Depth) | 65 x 65 x 1450 mm                         |
| Ingress protection code             | IP20/40 [Finger-protected;Wire-protected] |
| Mech. impact protection code        | IK04 [0.5 J standard plus]                |
| Optical cover type                  | Polycarbonate Diffuser                    |
| Net Weight (Piece)                  | 1.040 kg                                  |
| Approval and Application            |                                           |
| CE mark                             | Yes                                       |
| Ambient temperature range           | -20 to +40 °C                             |

# Coreline Slim Batten

| Initial Performance (IEC Compliant) |                             |
|-------------------------------------|-----------------------------|
| Luminous flux tolerance             | +/-10%                      |
| Power consumption tolerance         | +/-10%                      |
| Product Data                        |                             |
| Order product name                  | BN126C LED60S/840 PSU L1500 |
| Full product name                   | BN126C LED60S/840 PSU L1500 |
| Full product code                   | 692382863855999             |
| Order code                          | 911401899180                |

|                                 |                |
|---------------------------------|----------------|
| Material Nr. (12NC)             | 911401899180   |
| Local order code                | BN12660L8405FT |
| Numerator - Quantity Per Pack   | 1              |
| EAN/UPC - Product/Case          | 6923828638559  |
| Numerator - Packs per outer box | 6              |
| EAN/UPC - Case                  | 6923828638610  |

## Dimensional drawing

