



Coreline Slim Batten

BN126C LED60S/865 PSU L1500

Coreline Slim Batten, 46 W, 6000 lm, 6500 K

The new Philips Coreline slim batten offers exceptional value. It is Perfect for your everyday lighting installations. Available in 3 standard sizes, and 2 CCTs to provide flexibility to customer.

Product data

General Information	
Light source engine type	LED
Service tag	Yes
Light Technical	
Luminous Flux	6,000 lm
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	105 lm/W
Color rendering index (CRI)	>80
Light source color	865 cool daylight
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	46 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	30
Protection class IEC	Safety class I
Controls and Dimming	
Dimmable	No

Control interface	-
Mechanical and Housing	
Housing Material	Steel
Optical cover material	Polycarbonate
Housing Color	White RAL 9003
Optical cover finish	Opal
Overall length	1,450 mm
Overall width	65 mm
Overall height	65 mm
Dimensions (Height x Width x Depth)	65 x 65 x 1450 mm
Ingress protection code	IP20/40 [Finger-protected;Wire-protected]
Mech. impact protection code	IK04 [0.5 J standard plus]
Optical cover type	Polycarbonate Diffuser
Net Weight (Piece)	1.040 kg
Approval and Application	
CE mark	Yes
Ambient temperature range	-20 to +40 °C

Coreline Slim Batten

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	BN126C LED60S/865 PSU L1500
Full product name	BN126C LED60S/865 PSU L1500
Full product code	692382863856699

Order code	911401899280
Material Nr. (12NC)	911401899280
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828638566
Numerator - Packs per outer box	6
EAN/UPC - Case	6923828638627

Dimensional drawing

