

BN126C LED60S/865 PSU L1500

911401899280



Coreline Slim Batten, 46 W, 6000 lm, 6500 K

The new Philips Coreline slim batten offers exceptional value. It is Perfect for your everyday lighting installations. Available in 3 standard sizes, and 2 CCTs to provide flexibility to customer.

General Information

Light source engine type	LED
Service tag	Yes

Light Technical

Luminous Flux	6,000 lm
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	105 lm/W
Color rendering index (CRI)	>80
Light source color	865 cool daylight

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	46 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	30
Protection class IEC	Safety class I

Controls and Dimming

Dimmable	No
Control interface	-


Mechanical and Housing

Housing Material	Steel
Optical cover material	Polycarbonate
Housing Color	White RAL 9003
Optical cover finish	Opal
Overall length	1,450 mm
Overall width	65 mm
Overall height	65 mm
Dimensions (Height x Width x Depth)	65 x 65 x 1450 mm
Ingress protection code	IP20/40 [Finger-protected;Wire-protected]
Mech. impact protection code	IK04 [0.5 J standard plus]
Optical cover type	Polycarbonate Diffuser
Net Weight (Piece)	1.040 kg

Approval and Application

CE mark	Yes
Ambient temperature range	-20 to +40 °C

Dimensional drawing



Related Documents

Documents and certificates	Document Name	Download
Installation Instructions	BN126C-MI.pdf	Download 

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	BN126C LED60S/865 PSU L1500
Full product name	BN126C LED60S/865 PSU L1500
Full product code	692382863856699
Order code	911401899280
Material Nr. (12NC)	911401899280
Local order code	BN12660L8655FT
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828638566
Numerator - Packs per outer box	6
EAN/UPC - Case	6923828638627

