



Bright Star BVS211/ BVS221

BVS211 LED195/840 150W 220-240V GC

Bright Star BVS211/BVS221, 150 W, 20250 lm, 4000 K, Fixed Output

Philips Bright Star is a linear lighting solution designed specifically for indoor recreational sports venues, providing bright, anti-glare, and energy-efficient white light to enhance visibility and visual comfort for facilities such as badminton courts. Featuring a sleek, streamlined design, Bright Star provides clean, continuous illumination ideal for court lighting. Its one-piece stamped steel backplate guarantees structural strength, while the front optical design effectively controls glare in the direction of movement—perfectly balancing aesthetics and performance. With versatile installation options—including wall mount, suspension, and V-type dual-hanging adjustable-angle accessories—Bright Star offers flexible deployment to meet diverse lighting needs. This high-performance linear luminaire combines modern design, reliability, and superior lighting quality for an engaging indoor recreational sports experience.

Product data

General Information		Operating and Electrical	
Driver included	Yes	Beam angle of light source	90 degree(s)
Light source engine type	LED	Light source color	840 neutral white
Light Technical		Unified glare rating CEN	24
Luminous Flux	20,250 lm	Input Voltage	220-240 V
Correlated Color Temperature (Nom)	4000 K	Line Frequency	50 to 60 Hz
Luminous Efficacy (rated) (Nom)	135 lm/W	Power Consumption	150 W
Color rendering index (CRI)	80	Power Factor (Fraction)	0.95

Bright Star BVS211/BVS221

Connection	Flying leads/wires
Cable	Cable 1.0 m without plug
Number of products on MCB of 16 A type B	3
Protection class IEC	Safety class I

Controls and Dimming

Dimmable	No
Control interface	Fixed Output

Mechanical and Housing

Housing Material	Metal
Optical cover material	Polystyrene
Housing Color	White RAL 9003
Optical cover finish	Microprismatic lens
Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Microprismatic cover
Net Weight (Piece)	2.800 kg

Approval and Application

CE mark	No
Ambient temperature range	-20 to +45 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	BVS211 LED195/840 150W 220-240V GC
Full product name	BVS211 LED195/840 150W 220-240V GC
Order code	911401902476
Material Nr. (12NC)	911401902476
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6941970622875
Numerator - Packs per outer box	2
EAN/UPC - Case	6941970622875

Dimensional drawing

