Signify

EDP769 LED50/722 II MK-WH DM50 FG SRG10

912300024913

Heritage LED retrofit kit, 41 W, 3450 lm, 2200 K, CRI70, Distribution medium 50, Safety class II, IP66, SRG10-10

Aluminum, Black, Power supply unit (On/Off), 3450 lm, 41 W, 84 lm/W, 2200 K, (0.502, 0.415) SDCM <5, CRI70, Distribution medium 50, IP66 | Dust penetration-protected, jet-proof, IK09 | 10 J, Safety class II, Surge protection level until 10 kV differential mode and 10 kV common mode, Cable 0.5 m with cable connector, External connector

Warnings and Safety

- With the exception of integration of this product in Jargeau, Villa or Micenas 1 luminaire, conventional or LED variants, Signify N.V. cannot accept any liability with regards to the mechanical fixation of this product into any other luminaire or on/in any other mounting construction, and to all fixation related aspects. It is the sole responsibility of the customer to ensure that this product is mounted and fixed in a safe and reliable manner.

General Information

Lamp family code	LED50 [LED module 5000 lm]
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
Service tag	Yes
Lighting Technology	LED
Value ladder	Performance
Warranty period	5 years

Light Technical

Upward light output ratio	0.01
Luminous Flux	3,450 lm
Correlated Color Temperature (Nom)	2200 K
Luminous Efficacy (rated) (Nom)	84 lm/W
Color rendering index (CRI)	70
Light source color	722 warm white
Luminaire light beam spread	30° - 5° x 153°
Optic type outdoor	Distribution medium 50
Effective projected area	0 m²

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	46 A
Inrush time	0.25 ms
Power Consumption	41 W
Power Factor (Fraction)	0.97
Connection	External connector
Cable	Cable 0.5 m with cable connector
Number of products on MCB of 16 A type B	11
Protection class IEC	Safety class II
Surge Protection (Common/ Differential)	Surge protection level until 10 kV differential mode and 10 kV common mode

Controls and Dimming

Dimmable	No
Driver/power unit/ transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Maximum dim level	Not applicable

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Black
Mounting device	-
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	350 mm
Overall width	350 mm
Overall height	77 mm
Dimensions (Height x Width x Depth)	77 x 350 x 350 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Standard tilt angle posttop	-
Standard tilt angle side entry	-
Optical cover type	Flat glass
Net Weight (Piece)	3.610 kg

Approval and Application

Flammability mark	-
CE mark	Yes
ENEC mark	ENEC plus mark
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.502, 0.415) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤5

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L96

Sustainability Data

Sustainability rating	Unclassified
Repair class	Repair Class B, the driver and light source of this luminaire can be replaced by a service technician. Parts and documentation are available for an extended period of time.
Non-virgin material ratio of the packaging	Cardboard > 80% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80%
Packaging Material	Cardboard

Product Data

Order product name	EDP769 LED50/722 II MK-WH DM50 FG SRG10
Full product name	EDP769 LED50/722 II MK-WH DM50 FG SRG10
Full product code	871951422136900
Order code	912300024913
Material Nr. (12NC)	912300024913
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514221369
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514221369
Product family code	EDP769 [JARGEAU LED RETROFIT KIT]

Dimensional drawing



Polar normal diagrams



Related Documents

Documents and certificates	Document Name	Download
Installation Instructions	443000021523-583-EDP768-EDP769-Villa-Jargeau-LED-retrofit-kit-INI.pdf	Download

Photometry and lighting design	Document Name	Download
LDT File	LDT File - EDP768I - 912300024913.ldt	Download
ROLF File	ROLF File - EDP768I - 912300024913.rolfz	Download
ULD File	ULD File - EDP768I - 912300024913.uld	Download

© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.