PHILIPS

BVP111 LED51-4S/840
PSU OFA52 ALU C1KC3

912300060601

Coreline tempo small gen2, Floodlight, 33 W, 4101 lm, 4000 K, CRI80, Asymmetrical, IP66

Floodlight, Aluminum, Grey, Power supply unit (On/Off), 4101 lm, 33 W, 125 lm/W, 4000 K, (0.434, 0.403) SDCM <5, CRI80, Asymmetrical, IP66 | Dust penetration-protected, jet-proof, IK08 | 5 J vandal-protected, Safety class I, Surge protection level until 6 kV differential mode and 8 kV common mode, Cable 1.0 m with plug Wieland/Adels compatible 3-pole, External connector

General Information

Lamp family code	LED51 [LED module 5100 lm]
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
Service tag	Yes
Value ladder	Performance
Warranty period	5 years

Light Technical

Upward light output ratio	0
Luminous Flux	4,101 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	125 lm/W
Color rendering index (CRI)	80
Light source color	840 neutral white
Luminaire light beam spread	60° x 120°
Optic type outdoor	Asymmetrical
Effective projected area	0.02 m^2

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	18 A
Inrush time	0.3 ms
Power Consumption	33 W
Power Factor (Fraction)	0.97
Connection	External connector
Cable	Cable 1.0 m with plug Wieland/ Adels compatible 3-pole
Number of products on MCB of 16 A type B	30
Protection class IEC	Safety class I
Surge Protection (Common/ Differential)	Surge protection level until 6 kV differential mode and 8 kV common mode

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Grey
Mounting device	Wall-mounting bracket
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	286.9 mm
Overall width	211.5 mm
Overall height	64 mm
Dimensions (Height x Width x Depth)	64 x 212 x 287 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Optical cover type	Flat glass
Net Weight (Piece)	2.570 kg

Emergency Operation

Central Emergency	No
Emergency lighting	-

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-40 to +45 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.434, 0.403) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80

Sustainability Data

Sustainability rating	Unclassified
Repair class	Repair Class D, this product is not designed to be repaired.
Embedded carbon (A1-A3)	48.1 kg CO_2e
Product non-virgin material ratio	6.38 %
Recyclable content ratio of the finished product	52.5 %
GWP total B6 (kg CO2eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO2eq / kwh)
GWP total B6 (kg CO2eq) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) /lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO2 eq / kwh)
Non-virgin material ratio of the packaging	Cardboard > 80% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80%
Packaging Material	Cardboard

Product Data

Order product name	BVP111 LED51-4S/840 PSU OFA52 ALU C1KC3
Full product name	BVP111 LED51-4S/840 PSU OFA52 ALU C1KC3
Full product code	872016979978300
Order code	79978300
Material Nr. (12NC)	912300060601
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169799783
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169799783
Product family code	BVP111 [Coreline tempo small gen2]

Dimensional drawing



Polar normal diagrams



Related Documents

Documents and certificates	Document Name	Download
Tender text	Tender_Text_912300060601_en_BG.txt	Download
Installation Instructions	MI_Coreline tempo small gen2.pdf	Download
Environmental Product Declaration	EPD-Philips-Coreline-tempo-smallgen2-BVP111.pdf	Download

Photometry and lighting design	Document Name	Download
LDT File	LDT File - BVP111I - 912300060601.ldt	Download
ROLF File	ROLF File - BVP111I - 912300060601.rolfz	Download
ULD File	ULD File - BVP111I - 912300060601.uld	Download

© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.