



Beagency Brackets

JSB700 MBP-T 1100 60 RAL

Pole-mounting bracket 2 arms 180°, 1100 mm, 60 mm, 0°, RAL color, Mounting device diameter 1"

The Beagency bracket will perfectly fit in any medieval-inspired or historical environment thanks to a very ethereal, curvy and elegant shape.

Product data

Light Technical	
Effective projected area	0.25 m ²
Mechanical and Housing	
Fixation point length distance (Nom)	36 mm
Fixation diameter	Mounting device diameter 1"
Bracket tilt angle	0°
Bracket to luminaire diameter	60 mm
Bracket length	1100 mm
Bracket color	RAL color
Bracket type	Pole-mounting bracket 2 arms 180°
Net Weight (Piece)	18.000 kg
Approval and Application	
CE mark	Yes

EU RoHS compliant	Yes
Product Data	
Order product name	JSB700 MBP-T 1100 60 RAL
Full product name	JSB700 MBP-T 1100 60 RAL
Full product code	871869693268100
Order code	912401451161
Material Nr. (12NC)	912401451161
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696932681
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696932681

Beagency Brackets

Dimensional drawing

