



Kastelle Brackets

JSB710 MBP 800 60 RAL

Pole-mounting bracket, 800 mm, 60 mm, 0°, RAL color,
Mounting device diameter 1"

The Kastelle bracket has a very royal feel to it, reflecting the design of flag poles and thus conveying refinement to a whole lighting set.

Product data

Light Technical	
Effective projected area	0.185 m ²
Mechanical and Housing	
Fixation point length distance (Nom)	80 mm
Fixation diameter	Mounting device diameter 1"
Bracket tilt angle	0°
Bracket to luminaire diameter	60 mm
Bracket length	800 mm
Bracket color	RAL color
Bracket type	Pole-mounting bracket
Net Weight (Piece)	10.000 kg
Approval and Application	
CE mark	Yes

EU RoHS compliant	Yes
Product Data	
Order product name	JSB710 MBP 800 60 RAL
Full product name	JSB710 MBP 800 60 RAL
Full product code	871869693300800
Order code	912401451193
Material Nr. (12NC)	912401451193
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696933008
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696933008

Kastelle Brackets

Dimensional drawing

