



# Harmony Brackets

## JSP670 MBP-T 750 60 RAL

Pole-mounting bracket 2 arms 180°, 750 mm, 60 mm, 3°, RAL color, Mounting device diameter 1"

Harmony bracket is based on a clean shape and a modular construction. Different bracket styles, some dedicated to harmony LED luminaires and other compatible with any of our Philips luminaire, allow you to compose varied, yet consistent installations for classic and contemporary urban settings.

### Product data

Light Technical	
Effective projected area	0.13 m <sup>2</sup>
Mechanical and Housing	
Fixation point length distance (Nom)	20 mm
Fixation diameter	Mounting device diameter 1"
Bracket tilt angle	3°
Bracket to luminaire diameter	60 mm
Bracket length	750 mm
Bracket color	RAL color
Bracket type	Pole-mounting bracket 2 arms 180°
Net Weight (Piece)	9.922 kg
Approval and Application	
CE mark	Yes

EU RoHS compliant	Yes
Product Data	
Order product name	JSP670 MBP-T 750 60 RAL
Full product name	JSP670 MBP-T 750 60 RAL
Full product code	871869693451700
Order code	912401451346
Material Nr. (12NC)	912401451346
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696934517
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696934517

## Harmony Brackets

### Dimensional drawing

