

CR350Z SMB W60L60

912401483401



Cleanroom CR350B, Accessory, Steel, White

When operating a highly hygienic facility, the demands placed on light are very high and it must comply with strict standards; it must be easy to clean, dust-free, sealed and waterproof – all while offering exceptional optical performance. Philips CR350B Cleanroom luminaires are designed specifically for facilities where hygiene is critical, such as hospitals, laboratories, surgical and examination rooms, as well as applications in the pharmaceutical industry. These energy-efficient, durable cleanroom lighting solutions deliver excellent quality of light that complies with the strictest norms, as well as legislation that requires special IP65, easy-to-clean, dust-free luminaires. Thanks to excellent quality of light and colour rendering, Cleanroom luminaires also reduce eye strain. This can make all the difference in industries such as cleanroom production, graphics and textile manufacturing where high lumen and low glare light are so important.

General Information

Value ladder	Specification
--------------	---------------

Operating and Electrical

Input Voltage	- V
---------------	-----

Line Frequency	- Hz
----------------	------

Protection class IEC	-
----------------------	---

Mechanical and Housing

Overall length	630 mm
----------------	--------

Overall width	630 mm
---------------	--------

Overall height	145 mm
----------------	--------

Dimensions (height x width x depth)	145 x 630 x 630 mm
-------------------------------------	--------------------

Material	Steel
----------	-------

Ingress protection code	-
-------------------------	---

Mech. impact protection code	-
------------------------------	---

Accessory colour	White
------------------	-------

Angle	-
-------	---

Net Weight (Piece)	5.500 kg
--------------------	----------

Product Data

Order product name	CR350Z SMB W60L60
--------------------	-------------------

Full product name	CR350Z SMB W60L60
-------------------	-------------------

Full EOC	871869979753900
----------	-----------------

Order code	912401483401
------------	--------------

Material no. (12 NC)	912401483401
----------------------	--------------

Numerator – quantity per pack	1
-------------------------------	---

EAN/UPC — Product/Case	8718699797539
------------------------	---------------

Numerator – packs per outer box	1
---------------------------------	---

EAN/UPC - Case	8718699797539
----------------	---------------

Approval and Application

CE mark	Yes
---------	-----

EU RoHS compliant	Yes
-------------------	-----

Dimensional drawing

