



Emergency Bulkhead

EM153C SM BKD EXIT SIGN M3 ELB IP65

Emergency Bulkhead, 4 W, 4 W, 351x111 mm; H63 mm, 175 lm, 6500 K, IP65, ELB3h

351x111 mm; H63 mm, Polycarbonate, White, Signal white (RAL9003), 150 lm, 4 W, 50 lm/W, 6500 K, 0.33, Ribbed, UV stabilized Polycarbonate cover, IP65 | Dust penetration-protected, jet-proof, IK06 | 1 J, Safety class II, 2 Push-in connector 3-pole, Emergency lighting 3 hours duration basic version

Product data

General Information		Effective projected area	
Lamp family code	-		3 m ²
Number of gear units	1 unit	Operating and Electrical	
Driver included	Yes	Input Voltage	220-240 V
Light source engine type	LED	Line Frequency	50 Hz
Value ladder	Value	Initial CLO power consumption	4 W
Warranty period	5 years	Average CLO power consumption	3.2 W
Light Technical		End CLO power consumption	4 W
Upward light output ratio	0.77	Inrush current	4.96 A
Luminous Flux	150 lm	Inrush time	100 ms
Correlated Color Temperature (Nom)	6500 K	Power Consumption	4 W
Luminous Efficacy (rated) (Nom)	50 lm/W	Power Factor (Fraction)	0.4
Color rendering index (CRI)	>80	Connection	2 Push-in connector 3-pole
Light source color	6500	Cable	-
Optic type	-	Number of products on MCB of 16 A type B	273
Luminaire light beam spread	120°	Suitable for random switching	Not applicable
Optic type outdoor	-	Protection class IEC	Safety class II

Emergency Bulkhead

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	-
Control interface	Internal (no external connection)
Constant light output	No
Maximum dim level	Not applicable
Embedded control	-

Mechanical and Housing	
Housing Material	Polycarbonate
Reflector material	-
Optic material	Polycarbonate
Optical cover material	UV stabilized Polycarbonate cover
Fixation material	-
Housing Color	White
Mounting device	-
Optical cover finish	Ribbed
Reflector Finish	-
Overall length	351 mm
Overall width	111 mm
Overall height	63 mm
Dimensions (Height x Width x Depth)	63 x 111 x 351 mm
Parts color	All parts colored
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Optical cover type	-
Net Weight (Piece)	0.550 kg

Emergency Operation	
Emergency flux	175 lm
Rated duration of the emergency lighting (when fully charged)	3 hour(s)
Additional max. power consumption when emergency battery is charging	4 W
Central Emergency	No
Emergency lighting	Emergency lighting 3 hours duration basic version
Emergency function testing method	Manual / Test button
Emergency lighting operation mode	Maintained Non-maintained

Approval and Application	
Glow-wire test	-
Flammability mark	-
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 0 @ 200mm to EN62471
Photobiological risk specification	0 m
EU RoHS compliant	Yes

Performance ambient temperature Tq	25 °C
Ambient temperature range	+5 to +40 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-5%
Initial chromaticity	0.33
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 35000 h	5 %
Control gear failure rate at median useful life 50000 h	10 %
Control gear failure rate at median useful life 75000 h	25 %
Control gear failure rate at median useful life 100000 h	50 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 35000 h	L85
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L85
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 75000 h	L85
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L85

Sustainability Data	
Sustainability rating	Unclassified
Repair class	Repair Class D, this product is not designed to be repaired.
Non-virgin material ratio of the packaging	Cardboard > 80% recycled Plastic >35% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80% Plastic recycling rate > 40%
Packaging Material	Cardboard Plastic

Product Data	
Order product name	EM153C SM BKD EXIT SIGN M3 ELB IP65
Full product name	EM153C SM BKD EXIT SIGN M3 ELB IP65
Full product code	871869979895600
Order code	912401483510
Material Nr. (12NC)	912401483510
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699798956
Numerator - Packs per outer box	10
EAN/UPC - Case	8718699799939

Emergency Bulkhead

Dimensional drawing

