



Exit Sign

EM155Z SLIM WL EXIT SIGN LEGEND LEFT

IP00 | No protection, IK00 | No protection

Safety is important for building owners and therefore having proper emergency lighting in place is a major concern for them. The Exit Signs EM155C and EM159C offer an easy solution for standalone emergency lighting, that is fully compliant with European regulations. The lithium battery (LiFePO4) has many advantages over nickel based products, as it has a longer lifetime, better discharge behaviour, is produced in a more welfare friendly way and can be recycled. Legends, recessed mounting kit as well as suspension kit are available as accessories.

Product data

General Information		Initial CLO power consumption	
Lamp family code	-	Average CLO power consumption	- W
Number of gear units	-	End CLO power consumption	- W
Driver included	No	Connection	-
Light source engine type	-	Cable	-
Warranty period	5 years	Number of products on MCB (16 A type B)	-
Sustainability rating	Unclassified	Protection class IEC	-
		Surge Protection (Common/Differential)	-
Light Technical		Controls and Dimming	
Luminous Flux	0 lm	Dimmable	No
Correlated Colour Temperature (Nom)	-	Driver/power unit/transformer	-
Colour rendering index (CRI)	0	Control interface	-
Light source colour	-	Constant light output	No
Luminaire light beam spread	-	Maximum dim level	Not applicable
Optic type outdoor	-	Embedded control	-
Operating and Electrical			
Line Frequency	- Hz		

Exit Sign

Mechanical and Housing	
Housing material	Polyethylene
Reflector material	-
Optic material	-
Optical cover/lens material	-
Fixation material	-
Housing Colour	Green
Mounting device	-
Optical cover/lens shape	-
Optical cover/lens finish	-
Reflector finish	-
Overall length	314 mm
Overall width	158 mm
Overall height	1 mm
Dimensions (height x width x depth)	1 x 158 x 314 mm
Parts colour	All parts coloured
Ingress protection code	IP00 [No protection]
Mech. impact protection code	IK00 [No protection]
Standard tilt angle post-top	-
Standard tilt angle side entry	-
Optical cover type	-
Net Weight (Piece)	0.040 kg
Emergency Operation	
Emergency flux	0 lm
Central Emergency	Yes
Emergency lighting	-
Approval and Application	
Flammability mark	-
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 0 @ 200mm to EN62471


Photobiological risk specification	0 m
EU RoHS compliant	Yes
Ambient temperature range	+5 to +45 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-5%
Initial chromaticity	-
Init. Colour Rendering Index Tolerance	0

Over Time Performance (IEC Compliant)	
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 35000 h	-
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	-
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 75000 h	-
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	-

Product Data	
Order product name	EM155Z SLIM WL EXIT SIGN LEGEND LEFT
Full product name	EM155Z SLIM WL EXIT SIGN LEGEND LEFT
Full EOC	871869979901400
Order code	912401483516
Material no. (12 NC)	912401483516
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699799014
Numerator – packs per outer box	100
EAN/UPC - Case	8719514880030

Dimensional drawing



EM155Z

Exit Sign

