



# Exit Sign

## EM155Z SLIM WL EXIT SIGN LEGEND DOWN

IP00 | No protection, IK00 | No protection

Safety is important for building owners, and therefore having proper emergency lighting in place is a major concern for them. The Exit Signs EM155C and EM159C offer an easy solution for stand alone emergency lighting, that is fully compliant with European regulations. The lithium battery (LiFePO4) has many advantages over nickel based products, as it has a longer lifetime, better discharge behavior, is produced in a more welfare friendly way and can be recycled. Legends, recessed mounting kit as well as suspension kit are available as accessories.

### Product data

General Information		Average CLO power consumption	
Lamp family code	-	Average CLO power consumption	- W
Number of gear units	-	End CLO power consumption	- W
Driver included	No	Connection	-
Light source engine type	-	Cable	-
Warranty period	5 years	Number of products on MCB of 16 A type B	-
Light Technical		Protection class IEC	-
Luminous Flux	0 lm	Surge Protection (Common/Differential)	-
Correlated Color Temperature (Nom)	-	Controls and Dimming	
Color rendering index (CRI)	0	Dimmable	No
Light source color	-	Driver/power unit/transformer	-
Luminaire light beam spread	-	Control interface	-
Optic type outdoor	-	Constant light output	No
Operating and Electrical		Maximum dim level	Not applicable
Line Frequency	- Hz	Embedded control	-
Initial CLO power consumption	- W	Mechanical and Housing	
		Housing Material	Polyethylene

## Exit Sign

Reflector material	-
Optic material	-
Optical cover material	-
Fixation material	-
Housing Color	Green
Mounting device	-
Optical cover shape	-
Optical cover finish	-
Reflector Finish	-
Overall length	314 mm
Overall width	158 mm
Overall height	1 mm
Dimensions (Height x Width x Depth)	1 x 158 x 314 mm
Parts color	All parts colored
Ingress protection code	IP00 [No protection]
Mech. impact protection code	IK00 [No protection]
Standard tilt angle posttop	-
Standard tilt angle side entry	-
Optical cover type	-
Net Weight (Piece)	0.020 kg

### Emergency Operation

Emergency flux	0 lm
Central Emergency	Yes
Emergency lighting	-

### Approval and Application

Flammability mark	-
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 0 @ 200mm to EN62471
Photobiological risk specification	0 m
EU RoHS compliant	Yes

Ambient temperature range	+5 to +45 °C
---------------------------	--------------

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-5%
Initial chromaticity	-
Init. Color Rendering Index Tolerance	0

### Over Time Performance (IEC Compliant)

Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 35000 h	-
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	-
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 75000 h	-
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	-


### Sustainability Data

Sustainability rating	Unclassified
-----------------------	--------------

### Product Data

Order product name	EM155Z SLIM WL EXIT SIGN LEGEND DOWN
Full product name	EM155Z SLIM WL EXIT SIGN LEGEND DOWN
Full product code	871869979903800
Order code	912401483518
Material Nr. (12NC)	912401483518
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699799038
Numerator - Packs per outer box	100
EAN/UPC - Case	8719514880054

## Dimensional drawing



EM155Z

## Exit Sign

