

EM159Z WL/CM RECESSED KIT

912401483523



IP00 | No protection, IK04 | 0.5 J standard plus

Safety is important for building owners, and therefore having proper emergency lighting in place is a major concern for them. The Exit Signs EM155C and EM159C offer an easy solution for stand alone emergency lighting, that is fully compliant with European regulations. The lithium battery (LiFePO4) has many advantages over nickel based products, as it has a longer lifetime, better discharge behavior, is produced in a more welfare friendly way and can be recycled. Legends, recessed mounting kit as well as suspension kit are available as accessories.

General Information

Lamp family code	-
Number of gear units	-
Driver included	No
Light source engine type	-
Warranty period	5 years

Light Technical

Luminous Flux	0 lm
Correlated Color Temperature (Nom)	-
Color rendering index (CRI)	0
Light source color	-
Luminaire light beam spread	-
Optic type outdoor	-

Operating and Electrical

Line Frequency	- Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
End CLO power consumption	- W
Connection	-
Cable	-
Number of products on MCB of 16 A type B	-
Protection class IEC	-
Surge Protection (Common/Differential)	-

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	-
Control interface	-
Constant light output	No
Maximum dim level	Not applicable
Embedded control	-

Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	-
Optic material	-
Optical cover material	-
Fixation material	-
Housing Color	White RAL 9003
Mounting device	-
Optical cover shape	-
Optical cover finish	-
Reflector Finish	-
Overall length	350 mm
Overall width	82 mm
Overall height	45 mm
Dimensions (Height x Width x Depth)	45 x 82 x 350 mm
Parts color	All parts colored
Ingress protection code	IP00 [No protection]
Mech. impact protection code	IK04 [0.5] standard plus]
Standard tilt angle posttop	-
Standard tilt angle side entry	-
Optical cover type	-
Net Weight (Piece)	0.164 kg

Emergency Operation

Emergency flux	0 lm
Central Emergency	Yes
Emergency lighting	-

Approval and Application

Flammability mark	-
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 0 @ 200mm to EN62471
Photobiological risk specification	0 m
EU RoHS compliant	Yes
Ambient temperature range	+5 to +45 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-5%
Initial chromaticity	-
Init. Color Rendering Index Tolerance	0

Over Time Performance (IEC Compliant)

Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 35000 h	-
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	-
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 75000 h	-
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	-

Sustainability Data

Sustainability rating	Unclassified
Non-virgin material ratio of the packaging	Cardboard > 80% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80%
Packaging Material	Cardboard

Product Data

Order product name	EM159Z WL/CM RECESSED KIT
Full product name	EM159Z WL/CM RECESSED KIT
Full product code	871869979908300
Order code	912401483523

Material Nr. (12NC)	912401483523
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699799083
Numerator - Packs per outer box	50
EAN/UPC - Case	8719514880085

Related Documents

Documents and certificates	Document Name	Download
Installation Instructions	EM159Z-WL-CM-RECESSED-KIT-final.pdf	Download 

