



HID ignitors for series systems

SND 58 220-240V 50/60HZ


HID ignitors for series systems

Product data

Operating and Electrical		CE mark	No
Input Voltage	220 to 240 V	Ambient temperature range	-20 °C to 85 °C
Line Frequency	50 to 60 Hz	Product Data	
Input Frequency	50 to 60 Hz	Order product name	SND 58 220-240V 50/60Hz
Wiring		Full product name	SND 58 220-240V 50/60Hz
Connector Type	Screw	Full product code	871150093068230
Temperature		Order code	93068230
T-Case Maximum (Max)	90 °C	Material Nr. (12NC)	913700185166
Mechanical and Housing		Numerator - Quantity Per Pack	1
Housing	SNI-85	EAN/UPC - Product/Case	8711500930682
Net Weight (Piece)	0.050 kg	Numerator - Packs per outer box	48
Approval and Application		EAN/UPC - Case	8711500930699
Approval Marks	CE marking ENEC certificate		

HID ignitors for series systems

Dimensional drawing



Product	D1	C1	A1	A2	B1
SND 58 220-240V 50/60Hz	4.3 mm	38.5 mm	84.5 mm	65.0 mm	41.5 mm

