PHILIPS

Lighting

PrimaVision for SDW-TG

HID-PV 100 /S SDW-TG 220-240V 50/60Hz

Robust, lightweight and one-piece HID electronic gear for SDW-TG lamps (mini White SON) Lightweight, one-piece electronic gear for 50 and 100 W SDW-TG lamps (mini White SON)

Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Inrush Current Width	0.50 ms
Inrush Current Peak (Max)	33 A
Number of Products on MCB (16A Type B) (Nom)	14

Wiring	
Cable Length From Device to Lamp	2 m
Connector Type	Insert

Temperature	
T-Case Lifetime (Nom)	75 °C
T-Case Maximum (Max)	85 °C

Mechanical and Housing	
Housing	/S
Net Weight (Piece)	0.350 kg

Approval and Application	
Approval Marks	CE marking ENEC certificate CB Certificate
Ambient temperature range	-20 °C to 60 °C

Product Data	
Order product name	HID-PV 100 /S SDW-TG 220-240V 50/60Hz
Full product name	HID-PV 100 /S SDW-TG 220-240V 50/60Hz
Full product code	872790088754900
Order code	913700656566
Material Nr. (12NC)	913700656566
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500881861
Numerator - Packs per outer box	10
EAN/UPC - Case	8727900887549

PrimaVision for SDW-TG

Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
HID-PV 100 /S SDW-TG 220-240V 50/60Hz	4.5 mm	37.0 mm	150.0 mm	133.6 mm	90.0 mm	70.0 mm

© 2025 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.