OCC 0101A/02 DL BP Sensor WH

913701067103

Fast, Scalable and Future-ready smart lighting

Effortless Control with Signify Interact Ceiling-Mounted Sensors. Upgrade your smart lighting system with ease. Signify Interact ceiling-mounted wireless sensors deliver complete coverage exactly where you need it. Manage an entire group of connected luminaires and devices with a single sensor—or combine multiple sensors for ultimate flexibility. With the Interact app, zoning and re-zoning is simple and wire-free, giving you full control without limitations. The result? Exceptional energy savings and unmatched adaptability for any space.

Mechanical and Housing

Net Weight (Piece)	0.106 kg

Approval and Application

CE mark	Yes
EU RoHS compliant	Yes
Remarks	battery powered sensor, no need mains power input
Ambient temperature range	-5 °C to 45 °C

Application Conditions

Sensor Detection area shape	Rectangular
Minimum ceiling height (in m)	2 m
Maximum ceiling height - major motion (in m)	4 m
Maximum ceiling height - minor motion (in m)	4 m
Masking/shielding	Shield
Daylight regulation	Yes
Major motion detection area (in m)	At 4 m, detection area is 7.2 x 5.4 m
Minor motion detection area (in m)	At 4 m, detection area is 5.4 x 3.6 m
Wireless Technology	Zigbee

Product Data

Order product name	OCC 0101A/02 DL BP Sensor WH
Full product name	OCC 0101A/02 DL BP Sensor WH
Full product code	872016926059700
Order code	913701067103
Material Nr. (12NC)	913701067103
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169260597
Numerator - Packs per outer box	10
EAN/UPC - Case	8720169260610

Dimensional drawing

Related Documents

Documents and certificates	Document Name	Download
Installation Instructions	OCC010xA-Sensor-Installation-Instructions.pdf	Download

© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.