



EB-E Electronic ballasts for TL-D lamps (India)

EBE (Slim) 136 TLD 240V

Compact, lightweight, high-frequency electronic ballast for TL-D lamps

Product data


| Operating and Electrical | |
|---------------------------------|---------------------------------------------------------------------------------------------------|
| Input Voltage | 240 V |
| Line Frequency | 50 to 60 Hz |
| Input Frequency | 50 to 60 Hz |
| Wiring | |
| Connector Type Input Terminals | WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring] |
| Connector Type Output Terminals | WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring] |
| Temperature | |
| T-Case Maximum (Max) | 65 °C |
| Mechanical and Housing | |
| Net Weight (Piece) | 0.070 kg |

| Approval and Application | |
|---------------------------|-------------------|
| Energy Efficiency Index | Not specified |
| Safety Standard | - [Not specified] |
| Ambient temperature range | 0 °C to 50 °C |

| Product Data | |
|---------------------------------|-------------------------|
| Order product name | EBE (Slim) 136 TLD 240V |
| Full product name | EBE (Slim) 136 TLD 240V |
| Full product code | 871829111590800 |
| Order code | 913702242021 |
| Material Nr. (12NC) | 913702242021 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718291115908 |
| Numerator - Packs per outer box | 10 |
| EAN/UPC - Case | 8718291115908 |

EB-E Electronic ballasts for TL-D lamps (India)

Dimensional drawing



| Product | D1 | C1 | A1 | A2 | B1 |
|-------------------------|--------|---------|----------|----------|---------|
| EBE (Slim) 136 TLD 240V | 4.0 mm | 21.0 mm | 265.0 mm | 253.3 mm | 30.0 mm |

