

Micropower Electronic ballast for TL/PL-S/-T/-C lamps (India)

EBS 114 230 SH

Compact, lightweight, high-frequency electronic ballast designed for TL (6-18 W) and compact fluorescent PL (7-24 W) lamps


Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Wiring	
Connector Type Input Terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]
Connector Type Output Terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]
Temperature	
T-Case Maximum (Max)	75 °C
Mechanical and Housing	
Net Weight (Piece)	0.040 kg

Approval and Application	
Ambient temperature range	0 °C to 40 °C
Product Data	
Order product name	EBS 114 230 SH
Full product name	EBS 114 230 SH
Full product code	871150088496100
Order code	913702243012
Material Nr. (12NC)	913702243012
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500884961
Numerator - Packs per outer box	50
EAN/UPC - Case	8727900067989

Micropower Electronic ballast for TL/PL-S/-T/-C lamps (India)

Dimensional drawing



Product	D1	C1	A1	A2	B1
EBS 114 230 SH	4.0 mm	22.0 mm	80.0 mm	65.0 mm	40.0 mm

