

# HID-Basic Gearbox system for SON (India)

## BSN 070 M261

Impregnated electromagnetic ballasts of copper and steel construction for use in combination with an external ignitor for High-Pressure Sodium Vapor (SON) lamps

### Warnings and Safety

- Ballasts are only suitable for use with integrated luminaires

### Product data

Operating and Electrical	
Input Voltage	220/240 V
Line Frequency	50 Hz
Input Frequency	50 Hz

---

Wiring	
Connector Type	Screw

---

Mechanical and Housing	
Net Weight (Piece)	1.050 kg


---

Approval and Application	
Energy Efficiency Index	Not specified
Approval Marks	CE marking

Product Data	
Order product name	BSN 070 M261
Full product name	BSN 070 M261
Full product code	871150088440400
Order code	913702251012
Material Nr. (12NC)	913702251012
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500884404
Numerator - Packs per outer box	12
EAN/UPC - Case	8727900067378

## HID-Basic Gearbox system for SON (India)

### Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 070 M261	6.3 mm	51.0 mm	117.0 mm	98.0 mm	60.0 mm

