

HID-Basic BHL for HPL/HPI (India)

BHL 125 M261

Impregnated electromagnetic ballasts of copper and steel construction for High-Pressure Mercury Vapor (HPL) lamps

Product data

Operating and Electrical	
Input Voltage	220/240 V
Line Frequency	50 Hz
Input Frequency	50 Hz

Wiring	
Connector Type	Screw

Mechanical and Housing	
Net Weight (Piece)	1.045 kg

Approval and Application	
Energy Efficiency Index	Not specified

Product Data	
Order product name	BHL 125 M261
Full product name	BHL 125 M261
Full product code	871150088443500
Order code	913702251612
Material Nr. (12NC)	913702251612
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500884435
Numerator - Packs per outer box	12
EAN/UPC - Case	8727900067415

HID-Basic BHL for HPL/HPI (India)

Dimensional drawing



Product	D1	C1	A1	A2	B1
BHL 125 M261	6.3 mm	51.0 mm	117.0 mm	98.0 mm	60.0 mm

© 2026 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.