

HID-Basic BHL for HPL/HPI (India)

BHL 250 X261

Impregnated electromagnetic ballasts of copper and steel construction for High-Pressure Mercury Vapor (HPL) lamps

Product data

Operating and Electrical	
Input Voltage	240 V
Line Frequency	50 Hz
Input Frequency	50 Hz

Wiring	
Connector Type	Screw


Mechanical and Housing	
Net Weight (Piece)	2.110 kg

Approval and Application	
Energy Efficiency Index	Not specified
Approval Marks	CE marking

Product Data	
Order product name	BHL 250 X261
Full product name	BHL 250 X261
Full product code	871150088452700
Order code	913702253012
Material Nr. (12NC)	913702253012
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500884527
Numerator - Packs per outer box	4
EAN/UPC - Case	8727900067507

HID-Basic BHL for HPL/HPI (India)

Dimensional drawing



Product	D1	C1	A1	A2	B1
BHL 250 X261	6.3 mm	64.0 mm	132.0 mm	116.0 mm	75.0 mm

