

# HID-Basic Gearbox system for SON (India)

## BSN 250 M361

Impregnated electromagnetic ballasts of copper and steel construction for use in combination with an external ignitor for High-Pressure Sodium Vapor (SON) lamps

### Warnings and Safety

- Ballasts are only suitable for use with integrated luminaires

### Product data

Operating and Electrical	
Input Voltage	220/240 V
Line Frequency	50 Hz
Input Frequency	50 Hz

---

Wiring	
Connector Type	Screw

---

Mechanical and Housing	
Net Weight (Piece)	2.800 kg


---

Approval and Application	
Energy Efficiency Index	Not specified

Product Data	
Order product name	BSN 250 M361
Full product name	BSN 250 M361
Full product code	871150088467100
Order code	913702253722
Material Nr. (12NC)	913702253722
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500884671
Numerator - Packs per outer box	4
EAN/UPC - Case	8727900067675

## HID-Basic Gearbox system for SON (India)

### Dimensional drawing



Product	D1	C1	A1	B1	B2
BSN 250 M361	6.3 mm	64.0 mm	143.5 mm	77.5 mm	66.0 mm

