



Electronic Ignitors for HID lamp circuits (India)

SN 58/02

Electronic ignitors for HID lamps


Product data

Operating and Electrical	
Input Voltage	220/240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Temperature	
T-Case Maximum (Max)	80 °C
Mechanical and Housing	
Net Weight (Piece)	0.051 kg
Approval and Application	
Ambient temperature range	-20 °C to 90 °C

Product Data	
Order product name	SN 58/02
Full product name	SN 58/02
Full product code	871150099635000
Order code	913702261012
Material Nr. (12NC)	913702261012
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500996350
Numerator - Packs per outer box	50
EAN/UPC - Case	8727900068399

Electronic Ignitors for HID lamp circuits (India)

Dimensional drawing



Product	D1	C1	A1
SN 58/02	4.3 mm	37.5 mm	76.0 mm

