

# Electronic Ignitors for HID lamp circuits (India)

## IN124

Electronic ignitors for HID lamps


### Product data

Operating and Electrical	
Input Voltage	220/240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Temperature	
T-Case Maximum (Max)	90 °C
Mechanical and Housing	
Net Weight (Piece)	0.034 kg
Approval and Application	
Ambient temperature range	0 °C to 75 °C

Product Data	
Order product name	IN124
Full product name	IN124
Full product code	871150088413800
Order code	913702262012
Material Nr. (12NC)	913702262012
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500884138
Numerator - Packs per outer box	50
EAN/UPC - Case	8727900066968

## Electronic Ignitors for HID lamp circuits (India)

### Dimensional drawing



Product	B1	A1
IN124	38.0 mm	66.0 mm

