



Dynalite Signal Dimmer Controllers

DMBC110

The Dynalite range of Signal Dimmer Controllers, have been engineered to meet the future demands of projects. They are capable of transmitting all industry standard driver protocols (1-10V, DSI, DALI and Broadcast DALI) and support two ranges of install opportunities of both DIN-rail and wall box, to allow for flexible install opportunities. The Signal Dimmer Controller range also support a vast range of driver controllers with a variety of circuit numbers and sizes to work individually or as part of a system, suiting any project requirement.

Product data

Mechanical and Housing	
Net Weight (Piece)	0.700 kg
Approval and Application	
CE mark	Yes
EU RoHS compliant	Yes
Remarks	Please download the Lighting – Product Data Sheet for more information and ordering options
Ambient temperature range	0 to +50 °C
Product Data	
Order product name	DMBC110

Full product name	DMBC110
Full EOC	871016350636400
Order code	913703030009
Material no. (12 NC)	913703030009
Local order code	DMBC110
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8710163506364
Numerator – packs per outer box	1
EAN/UPC – Case	8710163506371

Dynalite Signal Dimmer Controllers

Dimensional drawing

