



Dynalite Signal Dimmer Controllers

DDBC516FR

The Dynalite range of Signal Dimmer Controllers, have been engineered to meet the future demands of projects. They are capable of transmitting all industry standard driver protocols (1-10V, DSI, DALI and Broadcast DALI) and support two ranges of install opportunities of both DIN-rail and wall box, to allow for flexible install opportunities. The Signal Dimmer Controller range also support a vast range of driver controllers with a variety of circuit numbers and sizes to work individually or as part of a system, suiting any project requirement.

Product data

Mechanical and Housing		Full product name		DDBC516FR
Net Weight (Piece)	0.330 kg	Full EOC		871016352310100
Approval and Application		Order code		913703031509
CE mark	Yes	Material no. (12 NC)		913703031509
EU RoHS compliant	Yes	Local order code		DDBC51
Remarks	Please download the Lighting – Product Data Sheet for more information and ordering options	Numerator – quantity per pack		1
Ambient temperature range	0 to +40 °C	EAN/UPC – Product/Case		8710163523101
Product Data		Numerator – packs per outer box		1
Order product name	DDBC516FR	EAN/UPC – Case		8710163523118

Dynalite Signal Dimmer Controllers

Dimensional drawing

