



# Dynalite Signal Dimmer Controllers

## DBC905W

The Dynalite range of Signal Dimmer Controllers, have been engineered to meet the future demands of projects. They are capable of transmitting all industry standard driver protocols (1-10V, DSI, DALI and Broadcast DALI) and support two ranges of install opportunities of both DIN-rail and wall box, to allow for flexible install opportunities. The Signal Dimmer Controller range also support a vast range of driver controllers with a variety of circuit numbers and sizes to work individually or as part of a system, suiting any project requirement.

### Product data

<b>Mechanical and Housing</b>	
Net Weight (Piece)	1.150 kg
<b>Approval and Application</b>	
CE mark	Yes
EU RoHS compliant	Yes
Remarks	Please download the Lighting – Product Data Sheet for more information and ordering options
Ambient temperature range	0 to +50 °C
<b>Product Data</b>	
Order product name	DBC905W

Full product name	DBC905W
Full EOC	871016350674600
Order code	913703040009
Material no. (12 NC)	913703040009
Local order code	DBC905W
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8710163506746
Numerator – packs per outer box	1
EAN/UPC – Case	8710163506753

# Dynalite Signal Dimmer Controllers

## Dimensional drawing

