



Dynalite Signal Dimmer Controllers

DBC905W

The Dynalite range of Signal Dimmer Controllers, have been engineered to meet the future demands of projects. They are capable of transmitting all industry standard driver protocols (1-10V, DSI, DALI and Broadcast DALI) and support two ranges of install opportunities of both DIN-rail and wall box, to allow for flexible install opportunities. The Signal Dimmer Controller range also support a vast range of driver controllers with a variety of circuit numbers and sizes to work individually or as part of a system, suiting any project requirement.

Product data

Mechanical and Housing		Full product name	
Net Weight (Piece)	1.150 kg	DBC905W	
Approval and Application		Full product code	
CE mark	Yes	871016350674600	
EU RoHS compliant	Yes	Order code	
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	913703040009	
Ambient temperature range	0 to +50 °C	Material Nr. (12NC)	
		913703040009	
Product Data		Numerator - Quantity Per Pack	
Order product name	DBC905W	1	
		EAN/UPC - Product/Case	
		8710163506746	
		Numerator - Packs per outer box	
		1	
		EAN/UPC - Case	
		8710163506753	

Dynalite Signal Dimmer Controllers

Dimensional drawing

