



Dynalite Sensors

DUS804CS-UP

The Philips Dynalite sensor range combines motion detection, light level detection and IR receive in one unit. Each of these features can be operated at the same time, allowing automation scenarios such as turning on the lights after detecting motion and then dimming the lighting level once the available sunlight has been measured, thereby providing additional energy savings. By combining each of these functions into one device, operational efficiency is improved. Each sensor has an in-built microprocessor, allowing logical functions to control one small room, the floor of a building, or an entire building. All sensors receive their power from the DyNet network, and as they are fully remotely programmable, they can be configured to automate and control a virtually unlimited number of controlled outputs.

Product data

Mechanical and Housing	
Net Weight (Piece)	83.500 g

Approval and Application	
CE mark	Yes
EU RoHS compliant	Yes
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options
Ambient temperature range	0 to +45 °C

Product Data	
Order product name	DUS804CS-UP

Full product name	DUS804CS-UP
Full product code	871016352202900
Order code	913703070409
Material Nr. (12NC)	913703070409
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163522029
Numerator - Packs per outer box	1
EAN/UPC - Case	8710163522036

Dynalite Sensors

Dimensional drawing

