



Dynalite Multipurpose Controllers

DMC2-UL

Within any project, many different lighting load types may be required to achieve a desired result. Each of these load types may require a different style of control. The Philips Dynalite range of multipurpose controllers allows customization of output types via different output module units. When using DIN-rail multipurpose controllers, a specific type of control can be chosen for each circuit: relay, leading-edge dimmer, trailing-edge dimmer, ballast control, controller with out-of-the-box functionality, fan control, and blind/screen control. In any combination, multiple load types can be controlled from a single device. This simplifies installation and prevents wasted capacity of circuits that are not required.

Product data

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Current (Nom)	32A per phase or single phase 63A max A
Mechanical and Housing	
Net Weight (Piece)	7.710 kg
Approval and Application	
CE mark	Yes
EU RoHS compliant	Yes
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options
Ambient temperature range	0 to +40 °C

Product Data	
Order product name	DMC2-UL
Full product name	DMC2-UL
Full product code	871869600701300
Order code	913703666009
Material Nr. (12NC)	913703666009
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696007013
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696014516

Dynalite Multipurpose Controllers

Dimensional drawing

