

**PHILIPS**

**Lighting**



# Dynalite Multipurpose Controllers

## DMP310GL-CE

Within any project, many different lighting load types may be required to achieve a desired result. Each of these load types may require a different style of control. The Dynalite range of multipurpose controllers allows customisation of output types via different output module units. When using DIN-rail multipurpose controllers, a specific type of control can be chosen for each circuit: relay, leading-edge dimmer, trailing-edge dimmer, driver control, controller with out-of-the-box functionality, fan control and blind/screen control. In any combination, multiple load types can be controlled from a single device. This simplifies installation and prevents wasted capacity of circuits that are not required.

### Product data

Mechanical and Housing	
Net Weight (Piece)	2.170 kg
Approval and Application	
CE mark	Yes
EU RoHS compliant	Yes
Remarks	Please download the Lighting – Product Data Sheet for more information and ordering options
Ambient temperature range	0 to +40 °C
Product Data	
Order product name	DMP310GL-CE

Full product name	DMP310GL-CE
Full EOC	871869600709900
Order code	913703666809
Material no. (12 NC)	913703666809
Local order code	DMP310
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696007099
Numerator – packs per outer box	1
EAN/UPC - Case	8718696014592

## Dynalite Multipurpose Controllers

### Dimensional drawing

